


## H50,0/41D BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Version	Wire-end ferrule, Standard, 31 mm, 25 mm, blue
Order No.	<a href="#">9019350000</a>
Type	H50,0/41D BL
GTIN (EAN)	4008 190049263
Qty.	50 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	3.26 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, blue	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	10.3 mm	Contact surface length (L2)	25 mm
Collar diameter (D2)	15 mm	Plastic collar thickness (S2)	0.5 mm
L1 in mm	41.00 mm	Wire connection cross section AWG, max.	AWG 1
Metal sleeve thickness (S1)	0.3 mm	Military designation	T 20A 035 A
Stripping length	31 mm	Conductor cross-section	50 mm <sup>2</sup>
Colour code	DIN		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

