


H1,0/14D R SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|----------------------------------------------|
| Version | Wire-end ferrule, Standard, 10 mm, 8 mm, red |
| Order No. | 9019420000 |
| Type | H1,0/14D R SV |
| GTIN (EAN) | 4008 190189099 |
| Qty. | 500 items |
| Packaging | Multipack bag |

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.11 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|-------------------------------------------|---------|----------|
| Description of article | Wire end ferrule with plastic collar, red | Version | Standard |
|------------------------|-------------------------------------------|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|----------|-----------------------------------------|-------------------|
| Contact surface diameter (D1) | 1.4 mm | Contact surface length (L2) | 8 mm |
| Collar diameter (D2) | 3 mm | Plastic collar thickness (S2) | 0.25 mm |
| L1 in mm | 14.00 mm | Wire connection cross section AWG, max. | AWG 17 |
| Metal sleeve thickness (S1) | 0.15 mm | Military designation | T 20A 009 A |
| Stripping length | 10 mm | Conductor cross-section | 1 mm ² |
| Colour code | DIN | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

