

CRIMPFIX LS PZ3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	9025300000
Type	CRIMPFIX LS PZ3
GTIN (EAN)	4008 190380335
Qty.	1 items

CRIMPFIX LS PZ3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	330 mm	Depth (inches)	12.9921 inch
Height	460 mm	Height (inches)	18.1102 inch
Width	390 mm	Width (inches)	15.3543 inch
Net weight	35000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

PW65 maintenance - automatic stripping/crimping

Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)	Drive	Electropneumatic
Pulse time	approx. 1 s	Wire end ferrules cross-section, max.	2.5 mm ²
Wire end ferrules cross-section, min.	0.5 mm ²	Crimping length	6/8/10 mm
Consumables	loose cable lugs	Length of wire-end ferrule	12/14/16 mm
Compressed-air connection	5 - 5.5 bar	Electrical connection	100-240 V / 50/60 Hz / 110 VA

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		