

H-BOX 0,5-2,5QMM DIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

General ordering data

Version	Assortment of wire end ferrules, Box, Colour code: DIN
Order No.	9025430000
Type	H-BOX 0,5-2,5QMM DIN
GTIN (EAN)	4008 190337 162
Qty.	1 items
Packaging	Box

H-BOX 0,5-2,5QMM DIN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Height	40 mm	Height (inches)	1.5748 inch
Diameter	92 mm	Net weight	73.04 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire-end ferrule box
------------------------	----------------------

Wire-end ferrules

Colour code	DIN
-------------	-----

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

H-BOX 0,5-2,5QMM DIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14D W	Version
Order No.	9019010000	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190120931	
Qty.	500 ST	
Type	H0,75/14D GR	Version
Order No.	9019040000	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190099077	
Qty.	500 ST	
Type	H1,0/14D R	Version
Order No.	9019080000	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190090623	
Qty.	500 ST	
Type	H1,5/14D SW	Version
Order No.	9019120000	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190153793	
Qty.	500 ST	
Type	H2,5/15D BL	Version
Order No.	9019160000	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190028732	
Qty.	500 ST	