




- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 26 mm, 21 mm, yellow
Order No.	9028200000
Type	H70,0/37 GE
GTIN (EAN)	4008190891572
Qty.	25 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	3.9 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	12.7 mm	Contact surface length (L2)	21 mm
Collar diameter (D2)	16 mm	Plastic collar thickness (S2)	0.6 mm
L1 in mm	37.00 mm	Wire connection cross section AWG, max.	AWG 2/0
Metal sleeve thickness (S1)	0.35 mm	Stripping length	26 mm
Conductor cross-section	70 mm ²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

