

POWERSTRIPPER 6,0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the insulation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Electric drive

General ordering data

Version	Tools, Automatic stripper
Order No.	9028510000
Type	POWERSTRIPPER 6,0
GTIN (EAN)	4008 190860752
Qty.	1 items

POWERSTRIPPER 6,0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	295 mm	Depth (inches)	11.6142 inch
Height	190 mm	Height (inches)	7.4803 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	7500 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Automatic stripping

Stripping range	0.05 - 6.0 mm ² (~ AWG 30-10)	
Conductor length, min.	22 mm + stripping length	
Connection values	46 VA	
Drive	electrical	
Pulse time	approx. 0.5 s	
Pull-off length	3-20 mm	
Electrical connection	100-240 V / 50/60 Hz / 70 VA	
Outer diameter of conductor	max.	5 mm

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

POWERSTRIPPER 6,0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

