

**CRIMP-SET PZ 6 ROTO L**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Crimp sets****General ordering data**

Version	Assortment crimping tool, Crimping tool: PZ 6 Roto L, Stripping tool: STRIPAX, Crimping range, min.: 0.14, Colour code: Weidmüller
Order No.	<a href="#">9028680000</a>
Type	CRIMP-SET PZ 6 ROTO L
GTIN (EAN)	4032248224746
Qty.	1 items
Packaging	Plastic box

## CRIMP-SET PZ 6 ROTO L

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	56 mm	Height (inches)	2.2047 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1735 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

### Technical data

Description of article	Set includes crimping tool, up to 6 mm <sup>2</sup> , lateral + frontal versions, stripping tool and wire-end ferrules in DIN colour code
------------------------	---

### Assortments

Crimping range, max.	6 mm <sup>2</sup>	Crimping range, min.	0.14 mm <sup>2</sup>
Packaging	Plastic box	Stripping tool	STRIPAX
Crimping tool	PZ 6 Roto L	Colour code	Weidmüller
Number of AEH	2850 pcs.		

### Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

## CRIMP-SET PZ 6 ROTO L

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

### General ordering data

Type	STRIPAX	Version	
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

### Crimping tools



- Crimping tools for wire end ferrules, with and without plastic collars
- Ratchet guarantees precise crimping
  - Release option in the event of incorrect operation

### General ordering data

Type	PZ 6 ROTO L	Version	
Order No.	<a href="#">1444050000</a>	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm <sup>2</sup> , 6mm <sup>2</sup> ,	
GTIN (EAN)	4050118248593	Trapezoidal crimp	
Qty.	1 ST		

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

## CRIMP-SET PZ 6 ROTO L

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H0,5/14 OR	Version
Order No.	<a href="#">0690700000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190015770	
Qty.	500 ST	
Type	H0,75/14 W	Version
Order No.	<a href="#">0462900000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190033248	
Qty.	500 ST	
Type	H1,0/14 GE	Version
Order No.	<a href="#">0463000000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190024697	
Qty.	500 ST	
Type	H1,5/14 R	Version
Order No.	<a href="#">0463100000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190065089	
Qty.	500 ST	
Type	H2,5/15D BL	Version
Order No.	<a href="#">9019160000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190028732	
Qty.	500 ST	

### Conductor nom. cross-section 6.0mm<sup>2</sup>



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H6,0/20 SW	Version
Order No.	<a href="#">0533500000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, black
GTIN (EAN)	4008190183905	
Qty.	100 ST	

### Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

## CRIMP-SET PZ 6 ROTO L

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	<a href="#">9028860000</a>	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		

### Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

### General ordering data

Type	EINSATZ A8-1 CL55	Version	
Order No.	<a href="#">9028460000</a>	Assortment of inserts	
GTIN (EAN)	4032248310029		
Qty.	100 ST		
Type	EINSATZ A7-1 CL55	Version	
Order No.	<a href="#">9028450000</a>	Assortment of inserts	
GTIN (EAN)	4032248310012		
Qty.	1 ST		

### Multi-bag



- In multi-pack bag
- Weidmüller colour code
- Other colour code

### General ordering data

Type	H4.0/18 GR SV	Version	
Order No.	<a href="#">9026010000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	
GTIN (EAN)	4008190117382		
Qty.	250 ST		