

CRIMP-SET PZ 6/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 6/5, Stripping tool: STRIPAX, Crimping range, min.: 0.25, Colour code: Weidmüller
Order No.	9028740000
Type	CRIMP-SET PZ 6/5
GTIN (EAN)	4032248368846
Qty.	1 items
Packaging	Plastic box

CRIMP-SET PZ 6/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1696.12 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Set includes crimping tool for up to 6 mm ² trapezoidal indent, stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	---

Assortments

Crimping range, max.	6 mm ²	Crimping range, min.	0.25 mm ²
Packaging	Plastic box	Stripping tool	STRIPAX
Crimping tool	PZ 6/5	Colour code	Weidmüller
Number of AEH	3100 pcs.		

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMP-SET PZ 6/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version	
Order No.	9005000000	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 6/5	Version	
Order No.	9011460000	Pressing tool, Crimping tool for wire-end ferrules, 0.25mm ² , 6mm ² ,	
GTIN (EAN)	4008190165352	Trapezoidal indentation crimp	
Qty.	1 ST		

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

CRIMP-SET PZ 6/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	H0,5/14D W	Version
Order No.	9019010000	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190120931	
Qty.	500 ST	
Type	H1,0/14D R	Version
Order No.	9019080000	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190090623	
Qty.	500 ST	
Type	H1,5/14D SW	Version
Order No.	9019120000	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190153793	
Qty.	500 ST	
Type	H0,75/14T HBL	Version
Order No.	9021040000	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190083168	
Qty.	500 ST	
Type	H2,5/19T GR	Version
Order No.	9021080000	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190149345	
Qty.	500 ST	
Type	H4,0/18T OR	Version
Order No.	9021100000	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4008190061708	
Qty.	500 ST	

Conductor nom. cross-section 6.0mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20T GN	Version
Order No.	9021130000	Wire-end ferrule, Standard, 14 mm, 12 mm, green
GTIN (EAN)	4008190111731	
Qty.	100 ST	