

**AM 12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Sheathing stripper for PVC cables

**General ordering data**

Version	Tools, Sheathing strippers
Order No.	<a href="#">9030060000</a>
Type	AM 12
GTIN (EAN)	4008190337827
Qty.	1 items

**AM 12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	10 mm	Depth (inches)	0.3937 inch
Height	46 mm	Height (inches)	1.811 inch
Width	97 mm	Width (inches)	3.8189 inch
Net weight	32.42 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Technical data**

Description of article	Sheathing stripper for UTP and STP data cables
------------------------	--

**Stripping tools**

Cable type	UTP and STP data cables	Copper cable - flexible, max.	4 mm <sup>2</sup>
Max. conductor diameter	12.5 mm	Min. conductor diameter	0.5 mm
Cut depth	adjustable	UTP und STP data cables, max. diameter	8 mm
Stripping range AWG, max.	11 AWG	Stripping range AWG, min.	18 AWG
Conductor cross-section, max.	122 mm <sup>2</sup>	Conductor cross-section, min.	0.2 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

**Example of use**



**Example of use**



**Example of use**

