

AM 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Sheathing stripper for PVC cables

General ordering data

Version	Tools, Sheathing strippers
Order No.	9030060000
Type	AM 12
GTIN (EAN)	4008190337827
Qty.	1 items

AM 12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	46 mm	Height (inches)	1.811 inch
Width	97 mm	Width (inches)	3.8189 inch
Net weight	32.42 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article Sheathing stripper for UTP and STP data cables

Stripping tools

Cable type	UTP and STP data cables	Copper cable - flexible, max.	4 mm ²
Max. conductor diameter	12.5 mm	Min. conductor diameter	0.5 mm
Cut depth	adjustable	UTP und STP data cables, max. diameter	8 mm
Stripping range AWG, max.	11 AWG	Stripping range AWG, min.	18 AWG
Conductor cross-section, max.	122 mm ²	Conductor cross-section, min.	0.2 mm ²

Classifications

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

Example of use



Example of use



Example of use

