



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

### General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, orange
Order No.	<a href="#">9037210000</a>
Type	H0,5/16 ZH OR
GTIN (EAN)	4008190492687
Qty.	500 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.12 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Twin wire end ferrule, orange	Version	Twin wire-end ferrule
------------------------	-------------------------------	---------	-----------------------

Wire-end ferrules

Contact surface diameter (D1)	1.4 mm	Contact surface length (L2)	10 mm
Collar width (B)	3 mm	Collar height (A)	5 mm
Plastic collar thickness (S2)	0.3 mm	L1 in mm	16.00 mm
Wire connection cross section AWG, max.	AWG 20	Metal sleeve thickness (S1)	0.15 mm
Stripping length	13 mm	Conductor cross-section	0.5 mm <sup>2</sup>
Colour code	Weidmueller		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

