

CUTTER 8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9040130000
Type	CUTTER 8
GTIN (EAN)	4008190467081
Qty.	1 items

CUTTER 8

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	65.5 mm	Height (inches)	2.5787 inch
Width	185 mm	Width (inches)	7.2835 inch
Net weight	168 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Front cable cutter up to 8 mm cable diameter	Version	One-hand mechanical
------------------------	--	---------	---------------------

Cutting tools

Copper cable - solid, max. (AWG)	6 AWG	Copper cable - solid, max.	16 mm ²
Copper cable - flexible, max. (AWG)	6 AWG	Copper cable - flexible, max.	16 mm ²
Copper cable - stranded, max. (AWG)	6 AWG	Copper cable - stranded, max.	16 mm ²
Copper cable, max. diameter	8 mm	Data / telephone / control cable, max. Ø	8 mm
Single-core aluminium cable, max.(mm ²)	16 mm ²	Stranded aluminium cable, max. (AWG)	6 AWG
Stranded aluminium cable, max (mm ²)	16 mm ²	Stranded aluminium cable, max. diameter	8 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		