

**CUTTER 8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

**General ordering data**

Version	Cutting tool for one-hand operation
Order No.	<a href="#">9040130000</a>
Type	CUTTER 8
GTIN (EAN)	4008190467081
Qty.	1 items

## CUTTER 8

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	65.5 mm	Height (inches)	2.5787 inch
Width	185 mm	Width (inches)	7.2835 inch
Net weight	168 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

### Technical data

Description of article	Front cable cutter up to 8 mm cable diameter	Version	One-hand mechanical
------------------------	--	---------	---------------------

### Cutting tools

Copper cable - solid, max. (AWG)	6 AWG	Copper cable - solid, max.	16 mm <sup>2</sup>
Copper cable - flexible, max. (AWG)	6 AWG	Copper cable - flexible, max.	16 mm <sup>2</sup>
Copper cable - stranded, max. (AWG)	6 AWG	Copper cable - stranded, max.	16 mm <sup>2</sup>
Copper cable, max. diameter	8 mm	Data / telephone / control cable, max. Ø	8 mm
Single-core aluminium cable, max.(mm <sup>2</sup> )	16 mm <sup>2</sup>	Stranded aluminium cable, max. (AWG)	6 AWG
Stranded aluminium cable, max (mm <sup>2</sup> )	16 mm <sup>2</sup>	Stranded aluminium cable, max. diameter	8 mm

### Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		