

CRIMPER 25 N D4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for non-insulated connectors
Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 10mm ² , 25mm ² , Indent crimp
Order No.	9040460000
Type	CRIMPER 25 N D4
GTIN (EAN)	4008 19046 1508
Qty.	1 items

CRIMPER 25 N D4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	250 mm	Width (inches)	9.8425 inch
Net weight	550 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for non-insulated connectors, 10-25 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Uninsulated connection	Conductor cross-section, max. AWG	AWG 4
Conductor cross-section, min. AWG	AWG 8	Crimping range, max.	25 mm ²
Crimping range, min.	10 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	25 mm ²	Crimping type/profile	Indent crimp
---------------------------------------	--------------------	-----------------------	--------------

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		