

## CRIMPER 25 Z

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

|            |  |
|------------|--|
| Version    | Tools, Crimping tool for wire-end ferrules, 6mm <sup>2</sup> , 25mm <sup>2</sup> , Trapezoidal crimp |
| Order No.  | <a href="#">9040470000</a>   |
| Type       | CRIMPER 25 Z   |
| GTIN (EAN) | 4008 19046 1485  |
| Qty.       | 1 items  |

**CRIMPER 25 Z**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |          |                |             |
|------------|----------|----------------|-------------|
| Width      | 250 mm   | Width (inches) | 9.8425 inch |
| Net weight | 529.57 g |                |             |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected                         |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 2159813b-98fd-4068-b62a-bc89a046c012 |

**Technical data**

|                        |                  |         |   |
|------------------------|------------------|---------|---|
| Description of article | (1)Crimping tool | Version | Mechanical, without interchangeable inserts |
|------------------------|------------------|---------|---|

**Description of contact**

|                      |                        |                      |                    |
|----------------------|------------------------|----------------------|--------------------|
| Type of contact      | Uninsulated connection | Crimping range, max. | 25 mm <sup>2</sup> |
| Crimping range, min. | 6 mm <sup>2</sup>      |                      |                    |

**tool data crimping**

|                                       |                    |                       |                   |
|---------------------------------------|--------------------|-----------------------|-------------------|
| Wire end ferrules cross-section, max. | 25 mm <sup>2</sup> | Crimping type/profile | Trapezoidal crimp |
|---------------------------------------|--------------------|-----------------------|-------------------|

**Important note**

|                     |   |
|---------------------|---|
| Product information | Crimping range 2 (with multiple crimping positions): 10 mm <sup>2</sup> , 2 x 4 mm <sup>2</sup> , 2 x 6 mm <sup>2</sup><br>Crimping range 4 (with multiple crimping positions): 16 mm <sup>2</sup> , 2 x 10 mm <sup>2</sup> |
|---------------------|---|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000168    | ETIM 9.0    | EC000168    |
| ETIM 10.0   | EC000168    | ECLASS 14.0 | 21-04-38-11 |
| ECLASS 15.0 | 21-04-38-11 |             |             |