

CRIMPER 25 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 6mm ² , 25mm ² , Trapezoidal crimp
Order No.	9040470000
Type	CRIMPER 25 Z
GTIN (EAN)	4008 19046 1485
Qty.	1 items

CRIMPER 25 Z

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	529.57 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	(1)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

Description of contact

Type of contact	Uninsulated connection	Crimping range, max.	25 mm ²
Crimping range, min.	6 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	25 mm ²	Crimping type/profile	Trapezoidal crimp
---------------------------------------	--------------------	-----------------------	-------------------

Important note

Product information	Crimping range 2 (with multiple crimping positions): 10 mm ² , 2 x 4 mm ² , 2 x 6 mm ² Crimping range 4 (with multiple crimping positions): 16 mm ² , 2 x 10 mm ²		
---------------------	---	--	--

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		