

CRIMPER 6 N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for non-insulated connectors

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm ² , 6mm ² , Trapezoidal crimp
Order No.	9040520000
Type	CRIMPER 6 N
GTIN (EAN)	4008 19046 146 1
Qty.	1 items

CRIMPER 6 N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	378.8 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for non-insulated connectors, 0.25-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Type of contact	Uninsulated connection	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	6 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	6 mm ²	Crimping type/profile	Trapezoidal crimp
---------------------------------------	-------------------	-----------------------	-------------------

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		