

CRIMPER 6 N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Crimping tools for non-insulated connectors
Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors
- Ratchet guarantees precise crimping
 - Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm ² , 6mm ² , Trapezoidal crimp
Order No.	9040520000
Type	CRIMPER 6 N
GTIN (EAN)	4008 19046 146 1
Qty.	1 items

CRIMPER 6 N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	378.8 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for non-insulated connectors, 0.25-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Type of contact	Uninsulated connection	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	6 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	6 mm ²	Crimping type/profile	Trapezoidal crimp
---------------------------------------	-------------------	-----------------------	-------------------

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		