

CRIMPER 6 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm ² , 6mm ² , Trapezoidal crimp
Order No.	9040530000
Type	CRIMPER 6 Z
GTIN (EAN)	4008 19046 1102
Qty.	1 items

CRIMPER 6 Z

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	377.61 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for wire-end ferrules 0,5 - 6mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, max.	6 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	6 mm ²	Crimping type/profile	Trapezoidal crimp
Crimping profile 5	6 mm ²		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		