

## CRIMPER 6 Z

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">9040530000</a>
Type	CRIMPER 6 Z
GTIN (EAN)	4008 19046 1102
Qty.	1 items

## CRIMPER 6 Z

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	377.61 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

### Technical data

Description of article	Crimping tool for wire-end ferrules 0,5 - 6mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

### Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, max.	6 mm <sup>2</sup>
Crimping range, min.	0.5 mm <sup>2</sup>		

### tool data crimping

Wire end ferrules cross-section, max.	6 mm <sup>2</sup>	Crimping type/profile	Trapezoidal crimp
Crimping profile 5	6 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		