

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

| | |
|------------|-------------------------------------|
| Version | Cutting tool for one-hand operation |
| Order No. | 9040560000 |
| Type | CUTTER 35 |
| GTIN (EAN) | 4008 190464943 |
| Qty. | 1 items |

CUTTER 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|--------------|
| Depth | 40 mm | Depth (inches) | 1.5748 inch |
| Height | 85 mm | Height (inches) | 3.3464 inch |
| Width | 290 mm | Width (inches) | 11.4173 inch |
| Net weight | 599.4 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

Technical data

| | | | |
|------------------------|---|---------|---------------------|
| Description of article | Front cable cutter up to 35 mm outer diameter | Version | One-hand mechanical |
|------------------------|---|---------|---------------------|

Cutting tools

| | | | |
|--|---------------------|--|---------------------|
| Copper sector cable | 3 x 70 SM | Copper cable - flexible, max. (kcmil) | 500 kcmil |
| Copper cable - flexible, max. | 240 mm ² | Copper cable - stranded, max. | 240 mm ² |
| Copper cable, max. diameter | 35 mm | Data / telephone / control cable, max. Ø | 35 mm |
| Aluminium sector cable | 4 x 70 SE | Stranded aluminium cable, max. (kcmil) | 500 kcmil |
| Stranded aluminium cable, max (mm ²) | 240 mm ² | Stranded aluminium cable, max. diameter | 35 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000142 | ETIM 9.0 | EC000142 |
| ETIM 10.0 | EC000142 | ECLASS 14.0 | 21-04-47-01 |
| ECLASS 15.0 | 21-04-47-01 | | |