

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9040560000
Type	CUTTER 35
GTIN (EAN)	4008 190464943
Qty.	1 items

CUTTER 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	290 mm	Width (inches)	11.4173 inch
Net weight	599.4 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Front cable cutter up to 35 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Copper sector cable	3 x 70 SM	Copper cable - flexible, max. (kcmil)	500 kcmil
Copper cable - flexible, max.	240 mm ²	Copper cable - stranded, max.	240 mm ²
Copper cable, max. diameter	35 mm	Data / telephone / control cable, max. Ø	35 mm
Aluminium sector cable	4 x 70 SE	Stranded aluminium cable, max. (kcmil)	500 kcmil
Stranded aluminium cable, max (mm ²)	240 mm ²	Stranded aluminium cable, max. diameter	35 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		