

STRIPSY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Sheathing stripper for PVC cables

General ordering data

Version	Sheathing strippers
Order No.	9042000000
Type	STRIPSY
GTIN (EAN)	4008190337834
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00
Alternative product	AM 12

STRIPSY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	46 mm	Height (inches)	1.811 inch
Width	97 mm	Width (inches)	3.8189 inch
Net weight	47.52 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping and cutting tool for data cable
------------------------	---

Stripping tools

Cable type	UTP and STP data cables	Copper cable - flexible, max.	4 mm ²
Max. conductor diameter	12.5 mm	Min. conductor diameter	0.5 mm
Cut depth	adjustable	UTP und STP data cables, max. diameter	8 mm
Stripping range AWG, max.	11 AWG	Stripping range AWG, min.	20 AWG
Stripping range, min.	0.08 mm ²	Conductor cross-section, max.	122 mm ²
Conductor cross-section, min.	1 mm ²		

Classifications

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		