

**SE HD 140****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

**General ordering data**

Version	Diagonal-cutting pliers
Order No.	<a href="#">9046310000</a>
Type	SE HD 140
GTIN (EAN)	4032248357611
Qty.	1 items

SE HD 140

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	140 mm	Width (inches)	5.5118 inch
Length	140 mm	Length (inches)	5.5118 inch
Net weight	180.1 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	Insulated diagonal-cutting pliers, 140 mm length	Version	One-hand mechanical
------------------------	--	---------	---------------------

Pliers

Conductor diameter, max. (H)	2 mm	Conductor diameter, max. (MH)	2.8 mm
Conductor diameter, max. (P)	1.4 mm	Cutter hardness	62 HRC
Protective insulation, 1000 V	Yes	Shape (diagonal-cutting pliers)	Standard
Total length	140 mm		

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

