

SE HD 160**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Version	Diagonal-cutting pliers
Order No.	9046320000
Type	SE HD 160
GTIN (EAN)	4032248357628
Qty.	1 items

SE HD 160

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	160 mm	Width (inches)	6.2992 inch
Length	160 mm	Length (inches)	6.2992 inch
Net weight	213 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated heavy-duty diagonal-cutting pliers, 160 mm long	Version	One-hand mechanical
------------------------	---	---------	---------------------

Pliers

Conductor diameter, max. (H)	2.3 mm	Conductor diameter, max. (MH)	3 mm
Conductor diameter, max. (P)	1.6 mm	Cutter hardness	62 HRC
Protective insulation, 1000 V	Yes	Shape (diagonal-cutting pliers)	Standard
Total length	160 mm		

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		