

RZ 160

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



up to 1000 V (AC) and 1500 V (DC)

protective insulation acc. to IEC 900. DIN EN 60900

- drop-forged from high-quality special tool steels
- safety handle with ergonomic and non-slip TPE VDE sleeve
- Made from shockproof, heat-and cold-resistant, non-flammable, cadmium-free TPE (thermoplastic elastomer)
- Elastic grip zone and hard core
- Highly-polished surface
- nickel-chromium electro-galvanised coating protects against corrosion

General ordering data

Version	Pliers
Order No.	9046360000
Type	RZ 160
GTIN (EAN)	4032248357666
Qty.	1 items

RZ 160

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	160 mm	Width (inches)	6.2992 inch
Net weight	120 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated round-nose pliers with long jaws
------------------------	--

Pliers

Protective insulation, 1000 V	Yes	Length of jaws	45 mm
Total length	160 mm		

Classifications

ETIM 8.0	EC000834	ETIM 9.0	EC000834
ETIM 10.0	EC000834	ECLASS 14.0	21-04-38-21
ECLASS 15.0	21-04-38-21		