

**FRZ SG 200****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pliers                     |
| Order No.  | <a href="#">9046400000</a> |
| Type       | FRZ SG 200                 |
| GTIN (EAN) | 4032248357710              |
| Qty.       | 1 items                    |

**FRZ SG 200**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

|            |          |                |            |
|------------|----------|----------------|------------|
| Width      | 200 mm   | Width (inches) | 7.874 inch |
| Net weight | 157.52 g |                |            |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected                         |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 8ca6a82a-a032-451b-b9c3-381eae86b1bb |

**Technical data**

|                        |  |
|------------------------|--|
| Description of article | VDE-insulated bent long-nose pliers with cutter, 200 mm long |
|------------------------|--|

**Pliers**

|                              |        |                               |        |
|------------------------------|--------|-------------------------------|--------|
| Conductor diameter, max. (H) | 1.8 mm | Conductor diameter, max. (MH) | 2.8 mm |
| Cutter hardness              | 60 HRC | Protective insulation, 1000 V | Yes    |
| Shape (telephone pliers)     | Bent   | Total length                  | 200 mm |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000835    | ETIM 9.0    | EC000835    |
| ETIM 10.0   | EC000835    | ECLASS 14.0 | 21-04-38-16 |
| ECLASS 15.0 | 21-04-38-16 |             |             |

Drawings

