

MEHA OB/UN 16² SPX 3**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Accessories, Cutter holder
Order No.	9054080000
Type	MEHA OB/UN 16² SPX 3
GTIN (EAN)	4008190022150
Qty.	1 items

MEHA OB/UN 16² SPX 3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	11.2 mm	Depth (inches)	0.4409 inch
Height	23 mm	Height (inches)	0.9055 inch
Width	30 mm	Width (inches)	1.1811 inch
Length	30 mm	Length (inches)	1.1811 inch
Net weight	6.98 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Cutter holder for Stripax 16
------------------------	------------------------------

Stripping tools

Colour	white	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	6 mm ²		

Classifications

ETIM 6.0	EC001509	ETIM 7.0	EC001509
ETIM 8.0	EC001509	ETIM 9.0	EC001509
ETIM 10.0	EC001509	ECLASS 9.0	21-04-92-37
ECLASS 9.1	21-04-48-90	ECLASS 10.0	21-04-92-37
ECLASS 11.0	21-04-48-91	ECLASS 12.0	21-04-48-91
ECLASS 13.0	21-04-48-91	ECLASS 14.0	21-04-48-91
ECLASS 15.0	21-04-48-91		