

LIR 6M10 V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6 mm ²
Order No.	9200270000
Type	LIR 6M10 V
GTIN (EAN)	4032248410095
Qty.	100 items

LIR 6M10 V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8.1 mm	Depth (inches)	0.3189 inch
Width	35.1 mm	Width (inches)	1.3819 inch
Net weight	2.1 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated ring-cable connector 6.0 mm ² / M10
------------------------	--

Connectors

Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Conductor cross-section	6 mm ²	Insulation	PVC, Available
Dimension (bolt)	M 10	Dimension	M 10
Material/plastic	PVC	Identification colour	yellow
Connection density (S1)	1 mm	Inside diameter (d1)	10.5 mm
Plastic collar length (b)	14.15 mm	Plastic collar diameter (D)	6.4 mm
Outside diameter (d)	15 mm		

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		