



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm ² - 1.5 mm ² , red
Order No.	9200300000
Type	LIS 1,5M3,5 V
GTIN (EAN)	40322484 10125
Qty.	100 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.8 mm	Depth (inches)	0.2283 inch
Width	21.6 mm	Width (inches)	0.8504 inch
Net weight	0.63 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated forked-cable connector 1.5 mm ² / M3.5
------------------------	---

Connectors

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Insulation	Available	Dimension (bolt)	M 3.5
Dimension	M 3.5	Material/plastic	PVC
Identification colour	red	Connection density (S1)	0.75 mm
Connection length (l)	17.8 mm	Inside diameter (d1)	3.7 mm
Plastic collar length (b)	11.3 mm	Plastic collar diameter (D)	4 mm
Outside diameter (d)	6.4 mm		

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

