

LIS 6M4 V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6 mm ² , yellow
Order No.	9200410000
Type	LIS 6M4 V
GTIN (EAN)	40322484 10255
Qty.	100 items

LIS 6M4 V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Width	25.9 mm	Width (inches)	1.0197 inch
Net weight	1.63 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated forked-cable connector 6.0 mm ² / M4
------------------------	---

Connectors

Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Insulation	Available	Dimension (bolt)	M 4
Dimension	M 4	Material/plastic	PVC
Identification colour	yellow	Connection density (S1)	1 mm
Connection length (l)	21.35 mm	Inside diameter (d1)	4.3 mm
Plastic collar length (b)	14.15 mm	Plastic collar diameter (D)	6.4 mm
Outside diameter (d)	9 mm		

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

