

## LIS 6M6 V


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow
Order No.	<a href="#">9200430000</a>
Type	LIS 6M6 V
GTIN (EAN)	40322484 10279
Qty.	100 items

## LIS 6M6 V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Width	32.6 mm	Width (inches)	1.2835 inch
Net weight	2.05 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Technical data

Description of article	Insulated forked-cable connector 6.0 mm <sup>2</sup> / M6
------------------------	---

## Connectors

Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
Insulation	Available	Dimension (bolt)	M 6
Dimension	M 6	Material/plastic	PVC
Identification colour	yellow	Connection density (S1)	1 mm
Connection length (l)	21.35 mm	Inside diameter (d1)	6.4 mm
Plastic collar length (b)	14.15 mm	Plastic collar diameter (D)	6.4 mm
Outside diameter (d)	12 mm		

## Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

