

LIS 6M10 V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6 mm ² , yellow
Order No.	9200450000
Type	LIS 6M10 V
GTIN (EAN)	4032248410293
Qty.	50 items

LIS 6M10 V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Width	36.7 mm	Width (inches)	1.4449 inch
Net weight	3.17 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated forked-cable connector 6.0 mm ² / M10
------------------------	--

Connectors

Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Insulation	Available	Dimension (bolt)	M 10
Dimension	M 10	Material/plastic	PVC
Identification colour	yellow	Connection density (S1)	1 mm
Inside diameter (d1)	10.5 mm	Plastic collar length (b)	13.15 mm
Plastic collar diameter (D)	6.4 mm	Outside diameter (d)	18 mm

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

