



Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm ² - 1.5 mm ² , red
Order No.	9200490000
Type	LIB 1,5B25 VF
GTIN (EAN)	40322484 10330
Qty.	100 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	1.16 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated joint connector 1.5 mm ² L=24.5 mm
------------------------	--

Connectors

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Insulation	Available	Dimension (pin length)	24.5 mm
Dimension	24.5 mm	Material/plastic	PVC
Identification colour	red	Plastic collar diameter (D)	3.8 mm

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

