



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² - 1.5 mm ² , red
Order No.	9200520000
Type	LIF 1,5F288 R
GTIN (EAN)	40322484 1036 1
Qty.	100 items

LIF 1,5F288 R

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.7 mm	Depth (inches)	0.2244 inch
Width	18.7 mm	Width (inches)	0.7362 inch
Net weight	0.62 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated tab-connector sleeves 1.5 mm ² / 2.8x0.8
------------------------	---

Connectors

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Conductor cross-section	1.5 mm ²	Insulation	Available, Partially insulated
Dimension (flat blade connector)	2.8 x 0.8 mm	Dimension	2.8 x 0.8 mm
Material/plastic	PVC	Identification colour	red
Plug-in width (d2)	2.8 mm	Plug-in density (d3)	0.8 mm
Plastic collar length (b)	10 mm	Plastic collar diameter (D)	4 mm

Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

Drawings

