



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> , 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> , red
Order No.	<a href="#">9200530000</a>
Type	LIF 1,5F488 R
GTIN (EAN)	40322484 10378
Qty.	100 items

## LIF 1,5F488 R

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	5.7 mm	Depth (inches)	0.2244 inch
Width	19.2 mm	Width (inches)	0.7559 inch
Net weight	0.71 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	Insulated tab-connector sleeves 1.5 mm <sup>2</sup> / 4.8x0.8
------------------------	---

### Connectors

Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Conductor cross-section	1.5 mm <sup>2</sup>	Insulation	Available, Partially insulated
Dimension (flat blade connector)	4.8 x 0.8 mm	Dimension	4.8 x 0.8 mm
Material/plastic	PVC	Identification colour	red
Plug-in width (d2)	4.8 mm	Plug-in density (d3)	0.8 mm
Plastic collar length (b)	10 mm	Plastic collar diameter (D)	4 mm

### Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

**Drawings**

