



Insulated tab connector made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ² , blue
Order No.	9200590000
Type	LIF 2,5M638 R
GTIN (EAN)	40322484 10439
Qty.	100 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6.3 mm	Depth (inches)	0.248 inch
Width	20.8 mm	Width (inches)	0.8189 inch
Net weight	0.7 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Cable lug connector 1.5-2.5 mm ²
------------------------	--

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Insulation	Available, Partially insulated	Dimension (flat blade connector)	6.3 x 0.8 mm
Dimension	6.3 x 0.8 mm	Material/plastic	PVC
Plug-in width (d2)	6.3 mm	Plug-in density (d3)	0.8 mm
Plastic collar length (b)	10 mm	Plastic collar diameter (D)	5 mm

Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

Drawings

