



Insulated tab-connector sleeves with branch, made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ² , blue
Order No.	9200620000
Type	LIF 2,5T638 R
GTIN (EAN)	40322484 10460
Qty.	100 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.7 mm	Depth (inches)	0.3031 inch
Width	20.8 mm	Width (inches)	0.8189 inch
Net weight	1.32 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Flat-blade receptacle with branch, 1.5 - 2.5 mm ²
------------------------	--

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Insulation	Available, Partially insulated	Dimension (flat blade connector)	6.3 x 0.8 mm
Dimension	6.3 x 0.8 mm	Material/plastic	PVC
Identification colour	blue	Plug-in width (d2)	6.3 mm
Plug-in density (d3)	0.8 mm	Plastic collar length (b)	10 mm
Plastic collar diameter (D)	5.8 mm		

Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		