

## HTF AFK 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for for turned/stamped contact

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

### General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.2mm <sup>2</sup> , 2.5mm <sup>2</sup> , B-Crimp
Order No.	<a href="#">9201040000</a>
Type	HTF AFK 2.5
GTIN (EAN)	4032248419678
Qty.	1 items

**HTF AFK 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	533 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Technical data**

Description of article	Crimping tool for AFK flat-blade contacts with opened crimping claws	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

**Description of contact**

Type of contact	Weidmüller FEKO ZRV	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	2.5 mm <sup>2</sup>
Crimping range, min.	0.2 mm <sup>2</sup>		

**tool data crimping**

Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Crimping type/profile	B-Crimp
---------------------------------------	---------------------	-----------------------	---------

**Classifications**

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

**Similar to illustration**

