



- supplied loose in polybag
- Weidmüller colour code

### General ordering data

Version	Wire-end ferrule, Standard, 18 mm, 14.5 mm, blue
Order No.	<a href="#">9202880000</a>
Type	H2,5/24 XS BL
GTIN (EAN)	4032248517954
Qty.	100 items
Packaging	loose

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 0.3 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Technical data**

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, blue	Version	Standard

**Wire-end ferrules**

Contact surface diameter (D1)	2.3 mm	Contact surface length (L2)	14.5 mm
Collar diameter (D2)	7.9 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	24.00 mm	Wire connection cross section AWG, max.	AWG 14
Metal sleeve thickness (S1)	0.15 mm	Stripping length	18 mm
Conductor cross-section	2.5 mm <sup>2</sup>	Colour code	Weidmueller

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

