


H10,0/22S EB**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 12 mm, Ivory
Order No.	9203620000
Type	H10,0/22S EB
GTIN (EAN)	403224856506 1
Qty.	100 items
Packaging	loose

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 0.51 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, special size, ivory	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	4.6 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	7.1 mm	Plastic collar thickness (S2)	0.6 mm
L1 in mm	22.00 mm	Wire connection cross section AWG, max.	AWG 8
Metal sleeve thickness (S1)	0.2 mm	Stripping length	15 mm
Conductor cross-section	10 mm ²	Colour code	Miscellaneous

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

