



- In multi-pack bag
- Weidmüller colour code
- DIN colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 6 mm, 6 mm, Turquoise |
| Order No. | 9204090000 |
| Type | H0,34/11 S TK |
| GTIN (EAN) | 4032248593026 |
| Qty. | 500 items |
| Packaging | loose |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.04 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| Description of article | Wire-end ferrule with plastic collar, special size, turquoise | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|----------------------|---|-------------|
| Contact surface diameter (D1) | 0.85 mm | Contact surface length (L2) | 6 mm |
| Collar diameter (D2) | 2.6 mm | Plastic collar thickness (S2) | 0.25 mm |
| L1 in mm | 11.00 mm | Wire connection cross section AWG, max. | AWG 22 |
| Metal sleeve thickness (S1) | 0.15 mm | Stripping length | 6 mm |
| Conductor cross-section | 0.34 mm ² | Colour code | Weidmueller |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

