

## KOBBS 19X55


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

Not suitable for stainless steel!

### General ordering data

Version	Sheet holes
Order No.	<a href="#">9205040000</a>
Type	KOBBS 19X55
GTIN (EAN)	4032248694273
Qty.	1 items

**Technical data**

**Dimensions and weights**

Height	55 mm	Height (inches)	2.1654 inch
Diameter	19 mm	Net weight	245 g

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

**Technical data**

Description of article	Tension screw with bearings 19.0 x 55.0 mm
------------------------	--

**Classifications**

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		