

LAN USB TESTER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Version	Testing tools, Continuity tester for data cables
Order No.	9205400000
Type	LAN USB TESTER
GTIN (EAN)	4032248732128
Qty.	1 items

LAN USB TESTER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	65 mm	Depth (inches)	2.5591 inch
Height	27 mm	Height (inches)	1.063 inch
Width	135 mm	Width (inches)	5.3149 inch
Net weight	355 g		

Temperatures

Operating temperature	
-----------------------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	2bc29d03-0968-4775-8c8f-2ea21fe4c041

Technical data

Description of article	Continuity testers
------------------------	--------------------

Measuring and testing devices

Supply	9V battery	Type of connection	RJ45, USB A, USB B
Display	LED	Protection degree	IP44
Tested and approved according to	EN/IEC 61010	Buzzer	No
Remote box dimensions	65 x 28 x 27 mm	Testable cable length, max.	1000 m
Remote box weight	30 g		

Classifications

ETIM 8.0	EC002080	ETIM 9.0	EC002080
ETIM 10.0	EC002080	ECLASS 14.0	27-20-11-08
ECLASS 15.0	27-20-11-08		

Drawings

Example of use



LAN USB TESTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Accessories

Accessories for testing and measuring equipment



General ordering data

Type	BLOCKBATTERIE 9V	Version	
Order No.	9004810000	Testing tools, Battery	
GTIN (EAN)	4008190050665		
Qty.	1 ST		