Data sheet

# SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M12 distributors are available in various versions. The 4, 6 or 8 M12 slots are in 4 or 5 pole design. The group outlet is designed as a fixed cable version, hood version for connection by the user, or with M23. Special versions are also available. For instance, there are 1-to-1 distributors for use with any connection types, or distributors approved for Ex Zone 1.

## General ordering data

| | |
|---|---|
| Version | Fixed cable version, M12, 30 V, A-coded, LED: Yes, LED initiator: Yes, Wiring type: PNP, 10 m |
| Order No. | 9456620000 |
| Type | SAI-06D-VPFC-5A-M12L-PNP-10U13 |
| GTIN (EAN) | 4008190304614 |
| Qty. | 1 items |

# Data sheet

## SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E141197 |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 127 mm | Depth (inches) | 5 inch |
| Height | 25 mm | Height (inches) | 0.9842 inch |
| Width | 60 mm | Width (inches) | 2.3622 inch |
| Net weight | 1294 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature | -20 - 80°C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Connection data

| | | | |
|---|---|---|---|
| Stripping length (sheathing) | 100 mm | Distributor outlet | Fixed cable version |

### Electrical data

| | | | |
|---|---|---|---|
| Rated voltage, min. | 10 V | Rated voltage, max. | 30 V |
| Test voltage | 1 kV | Max. current-carrying capacity per slot | 4 A |
| Total current | 9 A | Current per signal | 2 A |
| Electrical isolation available | No | Insulation resistance | 109 Ω |

### General technical data

| | | | |
|---|---|---|---|
| Protection degree | IP68 | Plug-in station coding | A-coded |
| Number of poles | 5 | Number of contact sockets | 6 |
| Connection thread | M12 | Pollution severity | 3 |
| Fire behaviour | V-0 | Plugging cycles | ≤ 50 |
| LED | Yes | LED initiator | Yes |
| LED colour for indicating operation | green | LED colour for I/O function | yellow |

### Material data

| | | | |
|---|---|---|---|
| Housing main material | Pocan | Material of distributor | Plastic |
| Housing colour | grey, RAL 7032 | Hood sealing material | Viton |
| Screw socket | Nickel-plated CuZn | Contact material | CuZn |
| Contact surface | Gold-plated | Contact carrier material | PBT (UL 94 V0) |

### Technical data cable

| | | | |
|---|---|---|---|
| Number of poles | 5 | Sheathing colour | black |
| O.D. | 8.8 mm | Shielded | No |

# Data sheet

## SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

| | | | |
|---|---|---|---|
| Halogen | No | Bending radius, min., moving | 10 x cable diameter |
| Bending cycles | 2 Mio | Wire cross section (Print/Online) | 12 x 0.34 mm² + 3 x 1.0 mm² |
| Sheath material | PUR | Colour coding | blue, brown, Green/yellow, white, green, yellow, grey, pink, red, grey / pink, red / blue, white / green, brown / green, white / yellow, Yellow / brown |
| Cable length | 10 m | Suitable for cable carriers | Yes |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC002585 | ETIM 9.0 | EC002585 |
| ETIM 10.0 | EC002585 | ECLASS 14.0 | 27-44-01-08 |
| ECLASS 15.0 | 27-44-01-08 | | |


# SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

## Drawings

### Dimensioned drawing




### Wiring diagram



# SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### M12



Protective caps protect unassigned plug-in stations against external influences.

#### General ordering data

| | | |
|---|---|---|
| Type | SAI-SK-M12 | Version |
| Order No. | 9456050000 | Protected component assemblies, Protective cap |
| GTIN (EAN) | 4008190304058 | |
| Qty. | 30 ST | |

### Screwty® cable gland tool with torque function



The ideal tool for any application
Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

#### General ordering data

| | | |
|---|---|---|
| Type | SCREWTY SET -DM | Version |
| Order No. | 1920000000 | Cable gland tool for M8, M12 lines and connectors |
| GTIN (EAN) | 4032248436859 | |
| Qty. | 1 ST | |


# SAI-06D-VPFC-5A-M12L-PNP-10U13

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.
Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.
Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

| | | |
|---|---|---|
| Type | ESG 9/20 MC NE WS | Version |
| Order No. | 1609940000 | ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable |
| GTIN (EAN) | 4008190203528 | |
| Qty. | 200 ST | |