



The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

#### Features:

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

#### General ordering data

|            |   |
|------------|---|
| Version    | TBF (polyester empty enclosure), Mounting plate, Mounting plate, Height: 134 mm, Width: 99 mm, Depth: 2 mm, Basic material: Sheet steel, galvanized, galvanized, silver |
| Order No.  | <a href="#">9502720000</a>  |
| Type       | MP TBF 19/15  |
| GTIN (EAN) | 4032248002139   |
| Qty.       | 1 items   |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 2 mm   | Depth (inches)  | 0.0787 inch |
| Height     | 134 mm | Height (inches) | 5.2756 inch |
| Width      | 99 mm  | Width (inches)  | 3.8976 inch |
| Net weight | 203 g  |                 |             |

**Temperatures**

|                       |
|-----------------------|
| Operating temperature |
|-----------------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                    |            |                |                         |
|--------------------|------------|----------------|-------------------------|
| Material thickness | 2 mm       | Type of fixing | when screwed in         |
| Surface finish     | galvanized | Basic material | Sheet steel, galvanized |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000213    | ETIM 9.0    | EC000213    |
| ETIM 10.0   | EC000213    | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 |             |             |