



The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

Features:

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|--|
| Version | TBF (polyester empty enclosure), Mounting plate, Mounting plate, Height: 550 mm, Width: 555 mm, Depth: 2 mm, Basic material: Sheet steel, galvanized, galvanized, silver |
| Order No. | 9502920000 |
| Type | MP TBF 60/60 |
| GTIN (EAN) | 4032248032334 |
| Qty. | 1 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 2 mm | Depth (inches) | 0.0787 inch |
| Height | 550 mm | Height (inches) | 21.6535 inch |
| Width | 555 mm | Width (inches) | 21.8503 inch |
| Net weight | 4620 g | | |

Temperatures

| |
|-----------------------|
| Operating temperature |
|-----------------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|------------|----------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000213 | ETIM 7.0 | EC000213 |
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ETIM 10.0 | EC000213 | ECLASS 9.0 | 27-40-06-39 |
| ECLASS 9.1 | 27-18-92-90 | ECLASS 10.0 | 27-40-06-39 |
| ECLASS 11.0 | 27-40-06-39 | ECLASS 12.0 | 27-40-06-39 |
| ECLASS 13.0 | 27-40-06-39 | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 | | |