

KISC M3X20.5/10 NI EK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Clamping yoke, Mounting screw
Order No.	9503280000
Type	KISC M3X20.5/10 NI EK4
GTIN (EAN)	4008 190550783
Qty.	100 items

KISC M3X20.5/10 NI EK4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	20.5 mm	Height (inches)	0.8071 inch
Width	4.8 mm	Width (inches)	0.189 inch
Net weight	1.15 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Colour grey

System specifications

Version Screws

Additional technical data

Installation advice Direct mounting Type of mounting when screwed in

Dimensions

Metric size of the thread, external 3.00 mm

General

Installation advice Direct mounting

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		