

MP MPC 12/17

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Mounting plates, 1.5 mm sheet steel, galvanized

General ordering data

Version	MPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 125 mm, Width: 175 mm, Basic material: Sheet steel, galvanized, galvanized
Order No.	9535560000
Type	MP MPC 12/17
GTIN (EAN)	4032248009299
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	125 mm	Height (inches)	4.9212 inch
Width	175 mm	Width (inches)	6.8898 inch
Net weight	165.8 g		

Temperatures

Operating temperature	
-----------------------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Type of fixing	when screwed in	Surface finish	galvanized
Basic material	Sheet steel, galvanized		

Classifications

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		

Accessories

TS 35

Accessories



General ordering data

Type	TS35X7.5 ST MPC1725 VER	Version	
Order No.	8000037600	Rail, TS 35, TS 35 x 7.5, Width: 90 mm, without slot, Steel, galvanic	
GTIN (EAN)	4050118653120	zinc plated and passivated	
Qty.	20 ST		

TS 15

Accessories



General ordering data

Type	TS15X5 ST MPC1217 VER	Version	
Order No.	8000037598	Rail, TS 15, Width: 4.13 mm, without slot, Steel, galvanized,	
GTIN (EAN)	4050118653106	chromium-plated	
Qty.	20 ST		