

FPC 20/20/13 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Medium-sized polycarbonate enclosures

The FPC series of enclosures is the next generation of the MPC series. Exhibiting the same material properties, the FPC series has an even wider range of accessories and hence extends the number of potential applications.

Features:

- 6 sizes in 2 versions
- Grey or transparent cover
- Cover with lead-seal holes
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails, mounting plates and PCBs
- Comprehensive accessories Weidmüller can manufacture and supply the enclosures to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Version	FPC (polycarbonate empty enclosure), Empty enclosure, Height: 200 mm, Width: 200 mm, Depth: 132 mm, Basic material: Polycarbonate, untreated, Light Grey, Transparent
Order No.	9535680000
Type	FPC 20/20/13 TRSP
GTIN (EAN)	4032248009794
Qty.	1 items

FPC 20/20/13 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	132 mm	Depth (inches)	5.1968 inch
Height	200 mm	Height (inches)	7.874 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	1074.48 g		

Temperatures

Operating temperature -50 °C...130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, right

M25	4	M63	1
M16	11	M40	1
M50	1	M32	2
M20	6	M12	20

Cable glands, top/bottom

M20	6	M12	20
M63	1	M40	1
M32	2	M25	4
M50	1	M16	11

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD) DE PS2420 220224 003ISS00

General information

Material thickness	3.5 mm	Operating temperature, max.	130 °C
Operating temperature, min.	-50 °C	Lid attachment	4 polyamide crosshead screws
Surface finish	untreated	Impact resistance	IK08
Protection degree	IP66, IP67	Basic material	Polycarbonate
Seal material	Polyurethane	Torque for lid screws	0.8 Nm
Integral fixing	thanks to self-tapping screws	Enclosure attachment	Holes 7.5 mm
Number of lid screws	4	Access opening: width	196.5 mm
Flange plate	No	Lid	Yes
Access opening: height	196.5 mm	Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction

FPC 20/20/13 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Technical data

www.weidmueller.com

horizontal assembly

WDU 10 / ZDU 10	1x8	WDU 16 / ZDU 16	1x7
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x17	WDU 35 / ZDU 35	1x5
WDU 4 / ZDU 4	1x14	WDU 6 / ZDU 6	1x10

vertical assembly

WDU 10 / ZDU 10	1x8	WDU 16 / ZDU 16	1x7
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x17	WDU 35 / ZDU 35	1x5
WDU 4 / ZDU 4	1x14	WDU 6 / ZDU 6	1x10

Classifications

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		

FPC 20/20/13 TRSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

